



注  
△ 海外向製品

型番	嵌合相手型番	仕上	$\phi D$	$L_1$	$L_2$	通用工具型番	製品規格番号	分類
170020-1	170021-1	電気錫めっき	3.5	17.0	7.3	2088544-1	108-5004	$\phi 4$
170020-2	170021-2	電気錫めっき	4.0	18.0	8.7	2088544-1	108-5003	$\phi 5$
170020-3	170021-3	—	4.0	18.0	8.7	2088544-1	108-5003	$\phi 5$
170020-4	—	—	3.5	17.0	7.3	2088544-1	108-5004 準拠	$\phi 4$

PRINT DIST  
単位: 耗 DIMENSIONS IN MM DO NOT SCALE PRINT

						参考図面 (CUSTOMER COPY) (REFERENCE ONLY)			
材料 (MATERIAL) 黄銅. 板厚 0.5			TE Connectivity						
仕上 (FINISH) 表参照			分類 (CLASS) 表参照						
包合電線断面積 (WIRE RANGE) 0.50 ~ 2.27 mm <sup>2</sup> (AWG #20 ~ #14)			型式 (TYPE) —						
被覆外径 (INSULATION DIA) 2.2 ~ 3.1 mm (— IN)			一般公差 (TOLERANCE) EXCEPT AS NOTED ±0.4 ±1°						
A1 REVISED PER ECO-11-005030			RK	HMR	25MAR11	LOD	SIZE	番号 (NO)	REV
LTR 変更 (REVISION RECORD)			DR.	CHK.	DATE	4-1	JA4	C-170020	A1
DR Y. Tanaka 1/22/14			DE						
CHK T. Suguchi 1/22/14			APP. Y. Sato 1/22/14						
名称 (NAME) Φ4 及び Φ5 シュア プラグ (shur plug)									