

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [98268-0265](#)
Status: **Active**
Overview: Premo-Flex™ FFC and Etched Polyimide Jumpers
Description: 1.25mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 20 Circuits, 0.152m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

Documents:

| | |
|--|--|
| Drawing (PDF) | Packaging Specification PK-98268-001 (PDF) |
| Product Specification PS-98268-001 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|-------------------------|---|
| Product Family | Cable |
| Series | 98268 |
| Comments | Contacts on the same side, Type A |
| Crimp Quality Equipment | Yes |
| Overview | <u>Premo-Flex™ FFC and Etched Polyimide Jumpers</u> |
| Product Name | Premo-Flex™ FFC Jumper |
| UPC | 756054777732 |

Physical

| | |
|-------------------------------|-----------------|
| Cable Length | 0.152m |
| Circuits (Loaded) | 20 |
| Net Weight | 2.632/g |
| Packaging Type | Bag |
| Pitch - Termination Interface | 1.25mm |
| Temperature Range - Operating | -40°C to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.4A |
| Voltage - Maximum | 60V AC |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|--------------|
| Packaging Specification | PK-98268-001 |
| Product Specification | PS-98268-001 |
| Sales Drawing | SD-98268-001 |



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed**

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[98268Series](#)

Use With

www.molex.com/link/ffc-fpc.html>Molex FFC – FPC connector. Be sure to match like plating