

# Datasheet

## 13 mm Corded Impact Drill

RS Stock number [534-8925](#)



### Features

- Rated power input: 600 W
- No-load speed: 0 - 2800 rpm
- Power output: 301 W
- Weight without cable: 1.7 kg
- Torque (soft screw driving applications): 10,8 Nm
- Rated torque: 1,8 Nm
- Drill spindle connecting thread: 1/2" – 20 UNF
- Chuck capacity: 1,5 - 13 mm
- Length: 266 mm
- Height: 180 mm
- Impact rate at no-load speed: 0 - 44800 bpm

### Drilling range

- Drilling dia. in concrete: 13 mm
- Drilling dia. in wood: 25 mm
- Drilling dia. in steel: 10 mm
- Drilling dia. in masonry: 15 mm