



ENGLISH

Datasheet

RS PRO 1,000PCS BOOTLACE FERRULE CRIMP TERMINAL KIT

Stock number: 228-0321



MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10	8
AMP.	9	12	17	18	30	35	50	70

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

CONNECTOR MATERIAL: COPPER TUBE.

INSULATION MATERIAL: NYLON

Bootlace Ferrule Kit Contents

	Wire Size	Colour	Quantity	PIN LENGTH	PIN DIA.	OVERALL LENGTH	Replacement Stock
1	0.5 mm ²	White	200	8 mm	1.3 mm	14.0 mm	458-689
2	0.75 mm ²	Blue	200	8 mm	1.5 mm	14.5 mm	458-695
3	1.0 mm ²	Red	200	8 mm	1.7 mm	14.5 mm	458-702
4	1.5 mm ²	Black	200	8 mm	2.0 mm	14.5 mm	458-718
5	2.5 mm ²	Grey	100	8 mm	2.5 mm	15.0 mm	458-724
6	4.0 mm ²	Orange	50	12 mm	3.2 mm	20.0 mm	458-730
7	6.0 mm ²	Green	30	12 mm	3.9 mm	20.0 mm	458-897
8	10.0 mm ²	Brown	20	12 mm	4.9 mm	22.0 mm	157-1244

1,000