



Datasheet

RS PRO Double Sided PVC Tape 25mm x 50m

Stock number: 2175258





General Description

The tape is a green PVC film with the faced side coated with a permanent dispersion acrylic adhesive and the unfaced side coated with a removable acrylic adhesive, interleaved with a white siliconised paper release liner. Ideal for short term carpet fixing for exhibitions.

Features

- NEC (National Exhibition Centre) approved
- Clean peel from most surfaces
- Easy unwind
- Conformable to awkward shapes
- UV resistant

Technical Details	Typical Values
Thickness	0.15 mm
Breaking Load	23 N/cm
Elongation	160%
Adhesion to steel faced side	6.0 N/cm
Adhesion to steel unfaced side	2.0 N/cm
RoHS compliant	Yes
Service Temperature	-5°C to +60°C
Application Temperature	0°C to +40°C
Storage Temperature	+12°C to +25°C

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.