



ENGLISH

Datasheet

RS Pro Cutter 138 mm

RS Stock No: **540-2013**



Product Details

RS Pro cutter measuring 138 mm, cuts and clenches the component lead ends by providing a permanent method of retaining components in a PCB. This special cutting and forming pliers has substantial pressed steel frames, chemically blackened, with return springs and plastic grips for easy, comfortable handling. The cutting edge is grounded to give precise cropping and manipulation of component leads. Tip is angled for easy access on to boards. The maximum cutting diameter of copper wire is 1 mm.

Features and Benefits

- Tips are angled for easy access on to boards
- 138 mm long
- Return springs and plastic grips for easy and comfortable handling
- 1.02 mm maximum cutting capacity



ENGLISH

Specifications:

Cutting Capacity Copper Wire	1.02 mm
ESD Safe	Yes
Maximum Cutting Capacity	1.02 mm
Overall Length	138 mm
Type	Cut & Press