



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 8:10 (UTC)



6014DDU

Single-Row Deep Groove Ball Bearings



Boundary Dimensions

d	70	mm	Bore diameter
D	110	mm	Outside diameter
B	20	mm	Width
r (min.)	1.1	mm	Chamfer dimension

Basic Load Ratings

Cr	42000	N	Basic dynamic load rating
C0r	31000	N	Basic static load rating

Speeds

Grease	3600	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	76.5	mm	Diameter of shaft abutment
da (max.)	80.5	mm	Diameter of shaft abutment
Da (max.)	103.5	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet

Calculation factors

fo	15.6		Factor
----	------	--	--------

Additional information

z	14		Number of Balls
Dw	11.906	mm	Ball Diameter

Mass

Mass approx.	0.608	kg	Mass approx.
--------------	-------	----	--------------

