



Main

Range of product	Odace
Aesthetic name	Kvadrat
Product or component type	Cover frame
Number of gangs	3 gangs
Installation direction	Horizontal/vertical
Distance between centers	71 mm
Type of frame	Triple
Type of packing	Flow-pack

Complementary

Device mounting	Flush
Fixing mode	Clip-in
Colour tint	Pearl grey
Side color	White (RAL 9003)
Surface finish	Matt
Surface treatment	Lacquered
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	85 mm
Width	227 mm
Depth	10 mm
Net weight	0.03601 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	2006/95/EEC UNE 20315-1-1 EN 60669-1 NF C 61-314 NBN C 61-112-1
Product certifications	AENOR: 030/2205 LCIE: NF 603415A N NF
IK degree of protection	IK04
IP degree of protection	IP21D

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations