

Datasheet

**RS Pro Multi Function 10 Time Delay Relay, Screw, 0.1 s
→ 100 h, SPDT, 1 Contacts, SPDT, 12 → 240 V ac/dc**
RS Stock No: **896-6813**



Product Details

RS Pro multi function 10 time delay relay is made to a high degree of precision and accuracy. The time settings can be set easily by using the knob on the front of the relay. It comes with a terminal screw and it has a time range of 0.1 s to 100 h with SPDT and SPDT switch configuration. It has 1 contact and supply voltage of 12 to 240 V ac/dc.

Features and Benefits

- Multifunction - 10 different modes
- 17.5 mm wide
- DIN rail mounting
- LED indications for power and relay status
- SPCO output relay
- 100 ms - 100 hours timing range
- IP20 (terminals), IP40 (enclosure) protection
- Wide voltage range

Specifications:

Number of Timer Functions	10
Power Supply	External
Switch Configuration	SPDT
Time Increment	Hours, Minutes, Seconds
Depth	65 mm
Length	85 mm
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-10°C
Number of Contacts	1
Width	18 mm
Contact Configuration	CO
Current Maximum	6 A
Current Minimum	0.1 A
Maximum Voltage	240 V ac/dc
Minimum Voltage	12 V ac/dc
Mode of Operation	Multi Function
Mounting Type	DIN Rail
Supply Voltage	12 to 240 V ac/dc
Terminal Type	Screw
Time Delay	200 (Reset) ms
Time Range	0.1 s to 100 h
IP Rating	IP20, IP40