



verso mobile drawer cabinet with 6 drawers & multiplex top. Featuring a robust, fully welded steel housing with push - pull handle, 100% extension drawers with drawer blocking and 125mm diameter castors. Drawer configuration: 3x 100mm, 2x 125mm, 1x 175mm (50kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 5010 gentian blue. WxDxH: 800x600x980mm

Breite [mm]: 800
Tiefe [mm]: 600
Höhe [mm]: 980
Bruttogewicht [kg]: 94.47
EAN-Code: 5039350027325
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Gentian blue
Main RAL colour	RAL 5010
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	6
Drawer load capacity [kg]	50
Drawer height 1 [mm]	100
Drawer height 2 [mm]	100
Drawer height 3 [mm]	100

Drawer height 4 [mm]	125
Drawer height 5 [mm]	125
Drawer height 6 [mm]	175

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Beech Multiplex
--------------------------	-----------------