



Product data sheet

Power tools for trade & industry

ANGLE EXACT ION 40-220

INDUSTRIAL ANGLE EXACT ION 40-220



The new EXACT screwdrivers – now with lithium-ion technology!

The most important data

Torque (hard)	20 – 40 Nm
Speed	22 – 220 rpm

Part Number 0 602 494 604

Technical data

Technical data

Description	Angle wrench
Torque, from (hard)	20 Nm
Torque, to (hard)	40 Nm
Torque (hard)	20 – 40 Nm
Torque, from (soft)	20 Nm
Torque, to (soft)	40 Nm
Torque (soft)	20 – 40 Nm
Speed, from	22 rpm
Speed, up to	220 rpm
Speed	22 – 220 rpm
Direction of rotation	R/L
Weight	2.4 kg
Comment	Below 50% speed setting eventually lower power
Bit holder	3/8 external square
Battery	18 V / 4.0 Ah battery
Drive type	Battery
Design	Angle
Connector type	Shut-off clutch

Noise/vibration information

Screwdriving

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

