

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [08-55-0102](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** [KK® 254 Crimp Terminal, 22-30 AWG, Bag, Selective Gold \(Au\), Nickel \(Ni\) Under Plating](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-10-07 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">2759</a>
Application	Signal
Crimp Quality Equipment	Yes
Overview	<a href="#">KK® Interconnect System - Molex</a>
Packaging Alternative	<a href="#">08-55-0101 (Reel)</a>
Product Name	KK® 254
UPC	800753745995

**Physical**

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.064/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm²	N/A

**Material Info**

Old Part Number [2759-\(555\)L](#)

**Reference - Drawing Numbers**

Product Specification	<a href="#">PS-10-07</a>
Sales Drawing	<a href="#">SD-2759</a>



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[2759Series](#)

**Use With**

[2695](#) , [5051](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0638118200</a>
Insertion Tool	<a href="#">0638120000</a>
Extraction Tool	<a href="#">0011030022</a>