

S-20 ; 0...6 bar gauge; 0 ... 10 V, 3-wire @ DC 12...35 V

S-20 ; 0...6 bar gauge; 0 ... 10 V, 3-wire @ DC 12...35 V

Item number: 14071202

Quantity: 1 pcs.

Order code: S-20-3-BG360-HSC3K-F-AGGZZZ-ZWZ W1011S20Z-ZZZZ31Z3-
SS1CLZ3APSZZE-ZZGFZZSAZZZS1

Overview: S-20 ; 0...6 bar gauge; 0 ... 10 V, 3-wire @ DC 12...35 V
Pressure transmitter Model S-20
Non-linearity: 0.25% BFSL
Overpressure limit: 3 times
Process connection: G 1/2 B EN 837 ; Sealing: copper
Pressure port: D 2.5 mm
Electrical connection: angular connector DIN 175301-803 A mating connector included
pin assignment el. connection: U+=1, U-=2, S+=3
Permissible medium temperature: -30...+100°C
shock and vibration resistance: 100 g shock, 20 g vibration
Approvals: cULus
Test protocol: with test protocol

Details: S-20 ; 0...6 bar gauge; 0 ... 10 V, 3-wire @ DC 12...35 V
Pressure transmitter Model S-20
Non-linearity: 0.25% BFSL
Overpressure limit: 3 times
Process connection: G 1/2 B EN 837 ; Sealing: copper
Pressure port: D 2.5 mm
Electrical connection: angular connector DIN 175301-803 A mating connector included
pin assignment el. connection: U+=1, U-=2, S+=3
Permissible medium temperature: -30...+100°C
shock and vibration resistance: 100 g shock, 20 g vibration
Approvals: cULus
Test protocol: with test protocol