

Accessories - "weatherproof" for outdoor installation

**DK KS 10**



- Rated connecting capacity: 2,5-16 mm<sup>2</sup>, Cu



- for insertion in cable junction boxes
- Terminal with 2 clamping units per pole
- current carrying capacity: 63 A
- 5-pole per pole 6 x 2.5 mm<sup>2</sup> sol, 4 x 4 mm<sup>2</sup> sol, 4 x 6 mm<sup>2</sup> sol, 4 x 10 mm<sup>2</sup> sol, 2 x 16 mm<sup>2</sup> s
- for cable junction boxes KF 10.. X
- complete with fixing elements
- lid fasteners sealable without accessories

rated insulation voltage	U <sub>i</sub> = 690 V a.c./d.c.
Dismantling length	11 mm
tightening torque for terminal	2,0 Nm
Weight	0,216 kg

**Drawings**

Dimension drawing

