

Features

- Material: UL94V-2 flame rated, UL approved Nylon 66 with adhesive tape.
- Color : Natural, available in other color.
- Application: Peel off the liner and fix the clip on the clamp on the dedicated area and fix the wire through Designed for installation of (1/4"dia.) RG-59(u) type cable.

RS PRO Self-Adhesive Wire Clip

RS Stock No.: 0268008



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This clip is designed to securely hold wires in place by peeling off the liner and sticking the clip onto a desired surface, making it ideal for cable management. It supports cable ties up to 9mm in width, with a maximum bundle diameter of 4mm. The product is available in natural colour and complies with RoHS and halogen-free certifications.

General Specifications

Bundle Diameter	4.0
Applicable Cable Tie Width	9.0
Colour	Natural
Material	Nylon 6/6
Application	Suitable for use in electrical and electronic servicing, maintenance, mechanical and automotive applications.

Mechanical Specifications

Size	¼" dia
Cable Type	RG-59(u)

Approvals

Standards Met	UL94V-2
---------------	---------

Similar Products