

Trolley jack 2 tons

RQGC10N

RQGC...


SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 ¤,-

<https://www.sam-outillage.com/>





DESCRIPTION

Trolley jack 2 tons

These jacks are equipped with a lowering control system.

Lifting capacity :

RQGCRB2: 2 tonnes

RQGCRB3: 3 tonnes

RQGC6N: 6 tonnes

RQGC10N: 10 tonnes

Polyamide wheels on RQGCRB2 and RQGCRB3 (Photo 1): floor protection.

Ergonomic handle on RQGC6N and RQGC10N (Photo 2)

Cups fitted with rubber pads to protect the contact surface. Ergonomic handle with grips on the handle for quick approach in all positions. Rubber protection on all jack heads. Complies with CE EN 1494 standard.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:21



SPECIFIC DATA

Designation	10T ROLLING JACK
Sales reference	RQGC10N
E (mm)	1600
Weight (kg)	111.5
C (mm)	605
H (mm)	386
D (mm)	1535
A (mm)	170
F (mm)	2530
Capacity	10T
B (mm)	270
G (mm)	414
Guarantee	2

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

L |

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
 42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

