

## FEATURES

- **45° Tip Angle:** Enhances precision and control during soldering tasks
- **11 mm Tip Length:** Suitable for reaching confined spaces on circuit boards
- **Hoof Tip Shape:** Ideal for drag soldering and spreading solder evenly
- **2 mm Tip Width:** Provides a balance between precision and coverage
- **Compliance with ANSI-ESD S20.20:2021:** Ensures electrostatic discharge protection
- **REACH and RoHS Compliant:** Meets environmental and safety standards

## RS PRO Soldering Iron Tip, 45° Angle, 11 mm Length

RS Stock No: 631-931



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO Soldering Iron Tip is designed for precision soldering tasks, offering a reliable solution for electronics assembly and repair. Its hoof shape and 45° angle provide excellent control and access to intricate components, ensuring efficient and accurate soldering.

## General Specifications

For Use With	492-303 Soldering Station
Product Type	Soldering Iron Tip
Tip Angle	45 °
Tip Series	T990
Tip Shape	Hoof

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, REACH, RoHS
---------------------	-----------------------------------

## Mechanical Specifications

Tip Length	11 mm
Tip Width	2 mm

