



Product data sheet

Power tools for trade & industry

Cordless Angle Grinder

PRO GWS 18V-8



Compact and swift, exceptional for everyday cutting tasks

The most important data

Battery voltage	18.0 V
No-load speed	11,000 rpm
Disc diameter	125 mm

Order number 0 601 9N9 000

Technical data

Additional data

Battery voltage	18.0 V
No-load speed	11,000 rpm
Disc diameter	125 mm
Grinding spindle thread	M14
Bore size, diameter	22.23 mm
Weight excl. battery	1.6 kg
X-LOCK	No
BITURBO	No

Noise/vibration information

Surface grinding (roughing)

Uncertainty K	1.5 m/s ²
---------------	----------------------

Sanding with sanding sheet

Uncertainty K	1.5 m/s ²
---------------	----------------------



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Convenient to use due to compact, lightweight design
- Boosts productivity thanks to fastest cutting performance for light applications
- Get more done on less recharges thanks to optimized runtime per charge
- More control and comfort with a new and improved sleek ergonomic grip
- Dust-free work thanks to metal flange compatibility with Bosch dust extractors



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/ao/en/wac/>

