


PAD30M3ABS - Break Stem Open

General Part Information		
Product Description		PAD30M3ABS
Article Number		62949.00
Rivet Type	i	Break Stem Open
Standard Bulk Pack Quantity		1000.00
Application / Features	i	

Geometry / Dimensions / Performance		
Head Style	i	Domed
Body Diameter Ø (mm)		3.00
Body Length (mm)		8.00
Min. Grip Range (mm)		3.20
Max. Grip Range (mm)		4.80
Min. Hole Diameter (mm)		3.10
Max. Hole Diameter (mm)		3.10
Min. Flange Diameter (mm)		5.70
Max. Flange Diameter (mm)		6.30
Flange Thickness (mm)		1.10
Mandrel Diameter (mm)		1.80
Nominal Shear Strength (N)		310.00
Nominal Tensile Strength (N)		420.00

Material / Finish / Weight		
Body Material	i	AlMg99.5
Mandrel Material		Aluminium
Finish		Clean
Weight per thousand (kg)		0.48

