




Part Number : [834219222](#)

Product Description : 9 Circuit Commercial Micro-D-to-9 Circuit Commercial Micro-D, Overmolded CAT 5 Cable, 1.20m Length

Series Number : 83421

Status : Active

Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings

[834219222_sd.pdf](#)

Specifications

[PS-83421-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	83421
Description	9 Circuit Commercial Micro-D-to-9 Circuit Commercial Micro-D, Overmolded CAT 5 Cable, 1.20m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Commercial Micro-D-to-Commerci
Product Name	Commercial Micro-D
UPC	756054711262

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	Per Wire Specification

Physical

Cable Length	1.20m
Circuits (Loaded)	9
Circuits (maximum)	9
Gender	Female-Female
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	1.138/g
Number of Rows	2
Overmolded	Yes
Packaging Type	Bag

Plating min - Mating	0.127µm
Plating min - Termination	1.270µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	CAT 5
Wire Size (AWG)	26