

Technical data sheet

Article number:
151-10913

QM40

Product Group	Cable tie mounts Q-Series
Product Family	Q-Mount Series QM, screwable
Material	Polyamide 6.6 (PA66)
Colour	Black (BK)
Fixation Method	Screw Mounting and Adhesive
Flammability	UL 94 V2
for Hole Ø (FH)	4.1 mm
Height (H)	5.5 mm
Length (L)	40.0 mm
Mounting Screw Type	M4 Screw
Operating Temperature	-40 °C to +85 °C
Package Content packed in	bag
Pack Cont.	50 pcs.
ROHS compliant	Yes
Width (W)	40.0 mm

HF ✓

RoHS ✓