

T SERIES

PAC^{TEC}[®]

8"



These new PacTec styles are ideal for a variety of handheld applications, including test equipment, meters, data entry terminals, and more. The various sizes have been designed to work with a

wide variety of LCDs, LEDs, and graphic displays. A waterproof "O" ring is available for NEMA 4X applications (not available on TR Models).

STANDARD OPTIONS

- Insert tooling areas
- Battery compartment
- Flame retardant materials
- EMI/RFI shielding
- Connector cutouts
- LCD adapters/bezels
- Custom panels & overlays
- Soft rubber protective holster
- 4AA, (2)9VB, 6AA availability
- Standard and custom membrane switches



T SERIES	WIDTH (mm)	LENGTH (mm)	HEIGHT (mm)
TR-9VB/2AA	111,8/83,8	195,58	31,75
TS	83,57	184,66	31,75
TS-9VB/2AA	83,57	184,66	31,75
TT	112,8/83,6	216,41	29,2/38,1
TT-9VB/2AA	112,8/83,6	216,41	29,2/38,1
TT1-(2)9VB/4AA	138,4/83,8	213,36	64,5/73,2
TT2-5AA	116,84	261,37	57,2/60,5

All dimensions are outside dimensions-in millimeters. T-Series units are available with a gasket for water-proofing the unit. Add G to the end of the part number when requesting a gasket.