



Part Number : [190430001](#)

Product Description : Double Male / Single Female Quick Disconnect Adapter, 6.35 x 0.81mm Tab Size, Non-Plated

Series Number : 19043

Status : Active

Product Category : Quick Disconnects

Engineering Number : MMFA



Documents & Resources

Drawings

[190430001_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19043
Description	Double Male / Single Female Quick Disconnect Adapter, 6.35 x 0.81mm Tab Size, Non-Plated
Product Name	Adapter
Style	Adapter
Type	Standard Quick Disconnect
UPC	800755059496

Electrical

Voltage - Maximum	N/A
-------------------	-----

Physical

Barrel Type	N/A
Gender	Dual
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Unplated

Material - Plating Termination	Unplated
Net Weight	1.579/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	0.81mm
Tab Width	6.35mm
Termination Interface Style	N/A
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----