Features

- 2:1 shrink ratio
- Operating temperature -55°C to 135°C
- Dielectric strength of 20 kV/mm
- Flame retardant (except clear)
- Excellent electrical, chemical, and physical properties
- Available in a wide range of colours

RS PRO PLF 100

RS Stock No



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS Pro PLF100 provides superior abrasion resistance when compared with that of many flexible, general purpose polyolefin tubings. This 2:1 ratio heat shrinkable sleeving has excellent physical and chemical properties that meet or exceed most of the common industrial and commercial standards.

General Specifications

Part Number	Ordering Size (mm)
0758123	1.6
0758132	1.6
0758128	1.6
0758124	2.4
0758129	2.4
0758120	3.2
0758127	3.2
0758122	3.2
0758121	4.8
0758130	4.8
0758126	4.8
0731144	6.4
0731126	6.4
0731146	6.4
0731145	6.4
0731137	9.5
0731127	9.5
0731139	9.5
0731141	9.5
0731128	12.7
0731140	12.7
0731136	12.7
0731142	12.7
0731138	12.7
0731129	19.0
0731133	19.0
0731134	19.0
0731135	19.0
0731130	25.4
0731124	25.4
0731122	25.4
0731125	25.4
0731123	25.4

Approvals

Specifications	UL 224 CSA LR31929 RoHS Compliant VW-1