



FLEXIBLE CUT METAL RECIPROCATING BLADES

P-04905

Steel, stainless steel, cast iron, alloys, steel pipe 1.2-2mm section.



TECHNICAL SPECIFICATIONS

Pack Quantity	5
Overall Length	150 mm
Aluminium	1.5 - 4 mm
Stainless Steel	1.2 - 3 mm
Mild Steel	1.5 - 4
Teeth per Inch	24

USER BENEFITS

- Fine cut in Steel, stainless steel, cast iron, alloys, steel pipe 1.2-2mm Section.
- Application: Steel, stainless steel, cast iron, alloys, steel pipe 1.2-2mm Section.
- Features: Bi-metal reciprocating blade, flexible to resist snapping, Cuts steel and alloy 24 Teeth per inch
- Tooth Type/Set: B - Milled and wavy set teeth

EAN 0088381914055

[Link to product - makitauk.com](https://www.makita.co.uk)

