



Deckplate Anti-Static

Hardwearing dual layer mat for static sensitive areas



- Hardwearing anti-fatigue mat for static sensitive areas.
- Conductive buried layer protects operatives and components.
- Diamond pattern surface is attractive and slip resistant.
- Top surface provides resilience to many industrial chemicals.
- Grounded via a 10 mm male stud fitted to the mat.
- Supplied with ramped edges as standard to reduce the risk of trips.
- Tested to EN14041 resistance requirements.
- Rv: 9.8 x 107 Ω



Parts

Part Number	Size	Colour	Weight
DPS010609	0.6 m x 0.9 m	Black	3.54 kg
DPS010915	0.9 m x 1.5 m	Black	8.86 kg
DPS010005	0.9 m x 18.3 m	Black	108 kg
DPS010005C	0.9 m x per linear metre	Black	8 kg
DPS010007	1.2 m x 18.3 m	Black	166 kg
DPS010007C	1.2 m x per linear metre	Black	9 kg

Technical Specification

Material	Vinyl top surface with PVC foam backing (fusion bonded, not glued)
Surface Finish	Diamond pattern
Product Height	14 mm
Operating Temperature	0°C to +60°C
Resistance to Chemicals	The PVC top surface provides limited resistance to chemicals and oils
Environmental Resistance	Suitable for dry indoor environments
Country of Origin	China