

**BOSCH**

Invented for life

Power tools for trade &amp; industry

## Product data sheet



Cordless Drill/Drivers

### GSR 18-2-LI Plus

Best price/performance ratio among professional cordless drill drivers

#### The most important data

Battery voltage	18 V
Max. screw diameter	8 mm
Torque, max. (hard/soft)	63 / 24 Nm

**Part number:** 0 601 9E6 170**GBP 123,00\***[> More product information](#)*\* Recommended retail price excluding VAT*

#### Technical data

Torque, max. (hard/soft)	63 / 24 Nm
No-load speed (1st gear / 2nd gear)	0 – 500 / 0 – 1.900 rpm
Chuck capacity, min./max.	1,5 / 13 mm
Drill spindle thread	1/2"
Battery voltage	18 V
Battery capacity	2,0 Ah
Weight incl. battery	1,5 kg
Torque settings	20+1
Length	191,0 mm
Height	230,0 mm
Cell type	Lithium-ion
Drilling diameter	
Max. drilling diameter in wood	38 mm
Max. drilling diameter in steel	13 mm
Screw diameter	
Max. screw diameter	8 mm

#### Noise/vibration information

Screwdriving	
Vibration emission value ah	2.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>
Drilling in metal	
Vibration emission value ah	2.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>




**BOSCH**

Invented for life

Power tools for trade & industry

**Advantages:**

- Attractive solution for the entry-level segment of professional applications
- Keyless chuck with 13mm bit holder for common accessories
- New ergonomics: Better handling due to compact design
- Bosch Electronic Cell Protection (ECP): protects the battery against overload, overheating and deep discharge
- Electronic Motor Protection (EMP) protects the motor against overload and ensures a long lifetime
- Integrated LED light for illuminating the work area, even in dark places



lightseries

**Prices / Scope of delivery**

Part number	0 601 9E6 170
1/2 L-BOXX inlay for accessories 1 600 A00 2WC	✓
1/2 L-BOXX inlay for tool 1 600 A00 2WA	✓
2 x 2.0 Ah Li-Ion batteries 1 600 Z00 036	✓
AL 1820 CV quick charger 2 607 225 426	✓
L-BOXX 136 1 600 A00 1RR	✓
<b>Price</b> (Recommended retail price excluding VAT)	<b>GBP 123,00</b>