



0.50MM LVDS FLAT FLEXIBLE CABLE (FFC)							
"L" DIM.→	51 ± 2 MM	102 ± 4 MM	152 ± 4 MM	203 ± 5 MM	254 ± 5 MM	305 ± 5 MM	610 ± 5 MM
REF DIM →	(2 INCHES)	(4 INCHES)	(6 INCHES)	(8 INCHES)	(10 INCHES)	(12 INCHES)	(24 INCHES)
CABLE TYPE →	A						
CKTS "N" ↓							
15	150210215	150210415	150210615	150210815	150211015	150211215	150212415
24	150210224	150210424	150210624	150210824	150211024	150211224	150212424
33	150210233	150210433	150210633	150210833	150211033	150211233	150212433



- | | | | | | | | | | | | | | | | |
|---|---|-------|-----------------|---|--------------------------------------|------------------------------|---|--|--|-----------------|-----------------|--|------------------------------|--|----------------------------|
| FUNCTIONAL SYMBOLS | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | | | | | | | | | | | | | |
|  | DIMENSION UNITS | | SCALE | | CURRENT REV DESC: PRODUCTION RELEASE | |  | | | | | | | | |
| | mm | | N/A | | | | | | | | | | | | |
| | GENERAL TOLERANCES (UNLESS SPECIFIED) | | | | | | 0.50MM PITCH LVDS FFC CABLE
SALES DRAWING | | | | | | | | |
| | | mm | INCH | | | | | | | | | | | | |
| | 4 PLACES | ±---- | ±---- | STATUS:---- | | PRODUCT SALES DRAWING | | | | | | | | | |
| | 3 PLACES | ±---- | ±0.01 | | | | | | | | | | | | |
| | 2 PLACES | ±---- | ±0.03 | | | DOCUMENT NUMBER
150210001 | | | | | | | | | |
| | 1 PLACE | ±---- | ±---- | | | | | | | DOC TYPE
PSD | | | | | |
| 0 PLACES | ±---- | ±---- | DOC PART
000 | | | | | | | | | | | | |
| ANGULAR TOL ± ---- ° | | | | | | | REVISION
A | | | | | | | | |
| DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS | | | | THIRD ANGLE PROJECTION
 | | DRAWING
C-SIZE | | | | | SERIES
15021 | | MATERIAL NUMBER
SEE CHART | | CUSTOMER
GENERAL MARKET |