

PRO HM 2620 E without restart protection

EAN 4007841 091255

Article number 091255



series 7

2300 W

2300 W Output

Display

Display (LCD)



50 – 700°C



stepless adjustable



150 – 500 l/min.



Suitable for screwable nozzles



CE



VDE

Function description

Power and advanced technology, the HeatMatic 2620 E hot air gun offers maximum precision for professional applications and is also lightweight, ergonomic and absolutely robust. With restart protection deactivated, this model is optimally designed for continuous repetitive use in a supervised environment.

Technical specifications

Temperature	50 – 700 °C
Airflow rate	150 – 500 l/min
Temperature setting	in 10°C steps by joystick
Settings made via	joystick
Temperature display	LCD display
Airflow control	Continuous
Programming function	Yes
Residual heat indicator	Yes
Cool function	Yes
Motor, type	Brushless
Heating element	Ceramic heating element
Mains power supply	220 – 230 V / 50 – 60 Hz
Function, hanger	No
Function, life expectancy, motor	10000 h

Function, life expectancy, heating element	800 h
Replaceable heating element	Yes
Restart protection	Yes
Fine dust filter	Yes
Thermal cut-out	Yes
Thermostat	Yes
Cord length	3 m
Dimensions (L x W x H)	358 x 91 x 95 mm
PU1, net weight	1,13 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841091255
Power plug	Typ E+F
Output	2300 W
Product category	Hot air tool

PRO HM 2620 E without restart protection

EAN 4007841 091255
Article number 091255



Accessories

EAN 4007841 092313	Round nozzle
EAN 4007841 009076	Round nozzle
EAN 4007841 011871	Soldering reflector nozzle
EAN 4007841 007812	Flat angled nozzle 20x2 mm, 100°
EAN 4007841 092115	Flat angled nozzle 20x2 mm - angled
EAN 4007841 092016	Flat angled nozzle 40x2 mm
EAN 4007841 009083	Flat nozzle 40x2 mm perforated
EAN 4007841 084967	Pressure roller Silicone Ø 35 mm
EAN 4007841 010423	Tarpaulin shears
EAN 4007841 009090	Flat nozzle 60x2 mm for bitumen
EAN 4007841 010409	Sieve reflector nozzle 50 x 35 mm
EAN 4007841 011857	Reflector nozzle 20mm
EAN 4007841 034986	Fillet testing device
EAN 4007841 092214	Round nozzle
EAN 4007841 011765	Fast welding nozzle 4mm narrow - for 5mm rd. noz.
EAN 4007841 011840	Fast welding nozzle 5mm narrow - for 5mm rd. noz.
EAN 4007841 010287	Fast welding nozzle 5mm - for 10mm rd. noz.