




RS Pro M12 Panel Mount Male 4W 300mm, PG9

RS Stock No: 144-7604





All dimensions are in mm.

General Specification		
Rated Operational Voltage	250 V	
Current Rating	4A	
Insulation Resistance	>= 100 MΩ	
Temperature Range	-25°C +75°C	
Degree of Protection	IP67	

	2 WHITE	
3 BLUE		−1 BROWN

4 BLACK

Pin Assignment

Material Specification	
Housing Material	Brass Ni Plated
Contact	Cu-Zn
Contact Plating	Gold Plated
Contact Carrier	Nylon 66
O-Ring	Neoprene
Pole	4
Clamp Nut	PG9

Cable Specification	
Cross Section of Wire	0.34 sq.mm
Termination	Partially Stripped
Cable length	300 mm