

UM-ALU 4-72 COVER PA BK - Lateral element



2200934

<https://www.phoenixcontact.com/gb/products/2200934>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Screw mounting, Side elements (left and right) incl. snap-on foot and screws for basic profile, width: 75.4 mm



Your advantages

- Aluminum extruded profile
- Variety of connection technology
- Can be mounted on the DIN rail
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- EMC protection

Commercial data

Item number	2200934
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ACHDFA
Product key	ACHDFA
Catalog page	Page 744 (C-1-2013)
GTIN	4046356716529
Weight per piece (including packing)	20.1 g
Weight per piece (excluding packing)	9.8 g
Customs tariff number	39269097
Country of origin	HU

UM-ALU 4-72 COVER PA BK - Lateral element



2200934

<https://www.phoenixcontact.com/gb/products/2200934>

Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM-ALU
Product family	UM-ALU 4-72
Type	Side elements (left and right) incl. snap-on foot and screws for basic profile
Ventilation openings present	no

Dimensions

Width	75.4 mm
-------	---------

Material specifications

Color (Housing)	black (RAL 9005)
Flammability rating according to UL 94	V0
Housing material	Polyamide
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Screw mounting
Tightening torque / speed	Screw connection with the basic profile: 0.8 Nm-1 Nm / rpm- rpm

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

UM-ALU 4-72 COVER PA BK - Lateral element



2200934

<https://www.phoenixcontact.com/gb/products/2200934>

Classifications

ECLASS

ECLASS-11.0	27182701
ECLASS-13.0	27190602

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-ALU 4-72 COVER PA BK - Lateral element



2200934

<https://www.phoenixcontact.com/gb/products/2200934>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk