

Mosaic™ mechanisms
single, multi-support power sockets: German and international standards



Selection chart for boxes, supports and plates (p. 812-813)

Pack	Cat.Nos	Multi-support single sockets - German standard
10	2 modules 772 10	With shutters for child protection (except Cat.No 772 10) For installation in flush-mounting box, surface mounting box, floor box, column module, desktop multi-outlet extension, office module and trunking 2P+E without shutters for child protection screw terminals
10	772 11	2P+E - Automatic terminals
10	772 13	2P+E with special tap-off screw and 4 mm ² screw terminals
10	772 45	2P+E angled at 45° - Automatic terminals
10	792 13	2P+E with aluminium finish cover plate screw terminals tamperproof
10	772 14	2P+E - Screw terminals
10	771 10	2P - Automatic terminals
10	772 19	2P+E with cover - Automatic terminals
10	772 12 ⁽¹⁾	2P+E with indicator ⁽¹⁾ - Screw terminals
10	772 16	2P+E green cover plate Automatic terminals
10	772 17	2P+E orange cover plate Automatic terminals
10	772 18	2P+E red cover plate Automatic terminals
10	1 module 771 50	2P ELV screw terminals Automatic terminals

Pack	Cat.Nos	Easy and simple actions 2P+E socket
1	5 modules 772 31	Special for disabled persons 2P+E socket Simple action on the lever allows easy plug-in or unplug

Pack	Cat.Nos	International standard power sockets
		Connection by screw terminals
10	1 module 775 01	Euro-US 2P
10	2 modules 775 02	2P+E
10	1 module 775 03	US 2P
10	2 modules 775 04	2P+E 15 A
10	2 modules 775 05	British 2P+E 13 A
10	1 module 775 10	Italian 2P+E 10 A on line
10	775 11	2P+E 10/16 A
10	2 modules 775 06	Swiss 2P+E type 13 Automatic terminals
10	2 modules 771 11	French 2P+E Automatic terminals

Pack	Cat.Nos	Anti-extraction module
1	1 module 770 80	When used with a socket, avoids accidental unplugging of sensitive electrical equipment, by gripping the cord (Ø4 to 8 mm cords) Can withstand an extraction force of 350 N (35 kgs)

Pack	Cat.Nos	Shaver sockets IP 24 - IK 04
1	5 modules 775 86	Conform to EN 60742 and EN 61558-2 Power supply 230 VA - 50/60 Hz and 1 output 120/220 V~. Connection via automatic terminals Equipped with a circuit separation transformer to isolate the user from the mains supply Protected against overloads and short circuits by built-in thermal relay limiting the available power to 20 VA. Insertion of the plug activates the power supply to the transformer With integrated support For flush mounting boxes only, use 2 gang box, 40 mm deep

(1) Indicator Cat.No 676 64 (see p. 546) supplied with the product