



### KEY FEATURES

- Dual core Atom CPU
- 2GB DDR 3 RAM
- 320GB HDD
- Windows 7 Pro

### SPECIFICATION

CPU	Intel Atom N2800 CPU, 1.86GHz dual core, 1MB cache, Fanless
Chipset	Intel NM10
Memory	2GB DDR3 RAM, Upgradeable to 4GB
Storage	320GB 2.5" SATA Hard Drive, 1x mSATA (shared with full size Mini PCIe)
I/O ports	<ul style="list-style-type: none"> <li>• 1 x VGA</li> <li>• 1 x HDMI</li> <li>• 1 x Gigabit LAN</li> <li>• 6 x USB 2.0</li> <li>• 2 x Audio</li> </ul>
Expansion slots	1 x full size Mini PCIe (shared with mSATA), 1x half size Mini PCIe
Power input	12V DC input, AC to DC adapter included
Operating system	Windows 7 Pro 32bit
Dimensions	190 x 205 x 83mm (D x W x H)
Operating temperature	0 to 45°C
Cooling	Fanless cooling

STE-WM-N28-SYS\_v2014\_01\_Rev2.pdf

Technical Specifications quoted are qualified and verified but do not indicate the maximum performance limitations of the equipment.  
Specifications are subject to change without notice. E & OE Issue A