

FPB

Article Number: 251-10209

Grommet, Panel Thickness .051"-.094", Polyethylene, Natural, 82ft/pkg



Download drawing

Base Data

Local Order Number	FPB
Type	G51PB
Color	Natural (NA)
Features and Benefits	<ul style="list-style-type: none"> • Can be cut to length with scissors, eliminating waste and keeping stock to a minimum. • Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.
Product Description	HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.
Variant	Open
Short Description	Grommet, Panel Thickness .051"-.094", Polyethylene, Natural, 82ft/pkg

Product Dimensions

Width W (imperial)	0.18 "
Width W (metric)	4.6 mm
Width W2 (imperial)	0.09 "
Width W2 (metric)	2.4 mm
Height H (imperial)	0.17 "
Height H (metric)	4.3 mm
Height H2 (imperial)	0.11 "
Height H2 (metric)	2.7 mm
Panel Thickness max. (imperial)	0.09 "
Panel Thickness max. (metric)	2.10 mm
Panel Thickness min. (imperial)	0.05 "
Panel Thickness min. (metric)	1.30 mm

Logistics and Packaging

Quantity per	roll
Package Quantity (imperial)	82 ft
Package Quantity	25 m
Carton Quantity	1 Reel
Weight (Metric)	0.33 kg

Material and Specifications

Material Polyethylene (PE)

Material Shortcut PE

Flammability UL94 HB

Halogenfree Yes

Operating Temperature -22°F to +176°F (-30°C to +80°C)

ROHS Conformity Yes