



**Part Number :** [1300910085](#)

**Product Description :** Woodhead Standard Duty Reel with Flying Leads, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length

**Series Number :** 130091

**Status :** Active

**Product Category :** Electrical Reels

**Engineering Number :** 997



---

## Documents & Resources

### Drawings

[1300910085\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Electrical Reels
Series	130091
Description	Woodhead Standard Duty Reel with Flying Leads, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length
Enclosure Rating	NEMA 1
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678833608

### Agency

CSA	LR29921
UL	E22769

### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	120V

### Physical

Bulb Included	N/A
Cable Length	0.457m (1.50')
Cable Movement	Ratchet Lock
Cord Length	10.67m (35.0')
Cord Type	12/3 SJTOW
Depth	0.30m (11.75")
Drum Lock	Ratchet
Duty	Standard
Guide Arm	2 - Position

Height	0.36m (14.25")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Net Weight	11793.392/g
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Width	196.85mm (7.750")
Wire Size (AWG)	12

---



---

This document was generated on Mar 27, 2025