



 PRODUCT-DETAILS

SP12/M16/M

STR SWL NPB FITTING M16 12MM-MET



General Information

Extended Product Type	SP12/M16/M
Product ID	7TCA296020R0061
EAN	5020963011665
Catalog Description	STR SWL NPB FITTING M16 12MM-MET
Long Description	5/16 Inch Nickel Plated Brass Straight Swivel Fitting with External Thread, Metric Thread Size M16

Additional Information

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

Ordering

EAN	5020963011665
UPC	786210259123

Technical

Number of Batteries	0
Color	Metallic
Material	Brass
Size	5/16 Inch

Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963011665
Package Level 1 Height	7.87 in 200 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	5.9 in 150 mm

Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

External Classifications and Standards

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

