



PRODUCT-DETAILS

SPL40/25M
40MM GS-PVC COAT CONDUIT 25M - BL



General Information	
Extended Product Type:	SPL40/25M
Product ID:	7TCA296030R0270
EAN:	5020963000973
Catalog Description:	40MM GS-PVC COAT CONDUIT 25M - BL
Long Description:	Liquid Tight, Oil Resistant, Medium Flexiblility Conduit, 1-1/4 Inch, Nominal Conduit Size 40mm, Outside Diameter 41.8mm, Inside Diameter 35.4mm, Static Bend Radius 180mm, Reel Length 25 Meters, PVC Covering with Galvanised Steel Core, Black
Display Name:	SPL40/25M

Additional Information	
Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Liquid Tight - Indoors / Outdoors, Marine, Buildings

Ordering	
EAN:	5020963000973

UPC: 786210247243

Dimensions

Outside Diameter: 41.8 mm

Technical

Number of Batteries: 0
Color: Black
Material: Galvanized Steel Core with PVC Covering

Environmental

WEEE Category: Product Not in WEEE Scope
RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece
Package Level 1 EAN: 5020963000973
Package Level 1 Height: 10.62 in
270 mm
Package Level 1 Depth / Length: 32.28 in
820 mm
Package Level 1 Width: 32.28 in
820 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618
RoHS Declaration: 9AKK107992A8994
REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose
ETIM 9: EC001179 - Protective metallic hose
UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

