

FEATURES

- 6.3mm x 32mm cartridge size
- F Speed Rating
- Cylindrical in shape
- HBC (high breaking current) fuse

RS PRO, 10A Ceramic Cartridge Fuse, 6.3 x 32mm, Speed FF

RS Stock No.: 420-218



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Cartridge Fuses



Product Description

RS PRO offer this range of miniature ceramic cartridge fuses which are either ultra-rapid fuses (FF) or fast acting fuses (F). The ultra-rapid fuses operate at higher temperatures so are ideal to provide circuit protection to semiconductor devices. The fast-acting fuses are ideal to protect less sensitive components.

General Specifications

Fuse Speed	FF
Body Material	Ceramic
Size Designation	Miniature
UL Class	UL 248-13
Applications	Miniature fuses are a relatively cheap way of protecting electrical equipment from short circuits and overcurrent and can be used to protect electrical appliances, electronic equipment and component parts

Electrical Specifications

Current Rating	10A
Voltage Rating	600V ac
High Rupture Capacity	Yes
Breaking Capacity (at Maximum Voltage Rating)	50kV

Mechanical Specifications

Fuse Size	6.3mm x 32mm
Overall Length	32mm
Diameter	6.3mm



Approvals

Compliance/Certifications	UL, RoHS
---------------------------	----------



