

Safety transformer, 63VA Primary 230 V AC, 50Hz, secondary 2x12 V/24 V AC With PTC fuse, 5 MW++



Model	
product brand name	SENTRON
product designation	Safety transformer
design of the transformer	Safety transformer
General technical data	
supplied active power / maximum	63 W
Voltage	
input voltage	230 V
output voltage	
• _1 / rated value	12 V
• _2 / rated value	24 V
Dissipation	
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	14 W
Current	
output current	
• maximum	5.2 A

- \_1 / rated value 5.2 A
- \_2 / rated value 2.6 A

### Suitability

suitability for integration	
<ul style="list-style-type: none"> <li>• surface-mounted installation</li> </ul>	No
<ul style="list-style-type: none"> <li>• flush mounting</li> </ul>	No

### Product details

product component / switch	No
----------------------------	----

### Product function

product function / thermal protection	Yes
---------------------------------------	-----

### Inputs Outputs

property of the output / short-circuit proof	Yes
--	-----

### Mechanical Design

height	64 mm
width	90 mm
length	90 mm
number of width units	5
mounting type / side-by-side mounting	Yes

### Certificates

**Declaration of Conformity**

**other**

[Confirmation](#)



EG-Konf.

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AC3763-0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4AC3763-0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=4AC3763-0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=4AC3763-0)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

