

Screw insert - SF-BIT-TX 10-50 - 1212573

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screw bit, Torx[®], E6.3-1/4" drive, size: TX 10 x 50 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

Your advantages

- Tools for SF-ASD 21 cordless screwdriver in various versions

Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 046356 590082
GTIN	4046356590082
Weight per Piece (excluding packing)	8.000 g
Custom tariff number	82079030
Country of origin	Czech Republic

Technical data

Dimensions

Length (b)	50 mm
Blade height	50 mm

General

Color	silver
Type	Torx
Material	alloyed tool steel
Test standard	DIN 3126

Standards and Regulations

Test standard	DIN 3126
---------------	----------

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Drawings

Screw insert - SF-BIT-TX 10-50 - 1212573

Pictogram



Classifications

eCl@ss

eCl@ss 10.0.1	21044290
eCl@ss 4.0	21040402
eCl@ss 4.1	21040402
eCl@ss 5.0	21040402
eCl@ss 5.1	21040400
eCl@ss 6.0	21049200
eCl@ss 7.0	21044290
eCl@ss 8.0	21044202
eCl@ss 9.0	21044290

ETIM

ETIM 4.0	EC002117
ETIM 5.0	EC002117

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01750
-----	--	--------------------------

