



## JetNet 3810G V2

### Industrial 8 FE + 2 GbE Unmanaged PoE Switch (Booster)

8 10/100 TX plus two 10/100/1000TX uplink ports  
 IP Surveillance with 8 IEEE802.3af PSE  
 12/24V Vehicle Power Input 48V Output  
 2 Gigabit Ports for Video Server/IPC connection  
 Port Link-Fault Alarm Digital Output  
 -40~70°C operating temperature

## Facts

### General description

|                   |                |
|-------------------|----------------|
| Part number       | F00N3810000001 |
| Life cycle status | Mature         |
| Warranty          | Up to 5 years  |

### Interface

|                     |                                  |
|---------------------|----------------------------------|
| Total ports number  | 10                               |
| 10/100TX ports      | 8                                |
| 10/100/1000TX ports | 2                                |
| DI/DO (dry relay)   | 1 relay DO with 1A/24VDC ability |
| DC power input      | 1 x DC 24V (8-32V)               |
| PoE ports           | 8                                |
| Power feeding mode  | 4578 (B)                         |
| PoE mode            | IEEE 802.3af                     |
| System PoE budget   | 80W@8-32V 70°C                   |

## Features

|             |           |
|-------------|-----------|
| Switch type | Unmanaged |
|-------------|-----------|

## SW/Protocol

|             |            |
|-------------|------------|
| Event alarm | Port Alarm |
|-------------|------------|

## Mechanical

|                         |                  |
|-------------------------|------------------|
| Housing/protection (IP) | IP30 Aluminum    |
| Dimension (HxWxD mm)    | 149 x 66 x 131.2 |
| Mounting                | DIN Rail         |
| Operating temperature   | -40~70°C         |

## Certification

|                     |                          |
|---------------------|--------------------------|
| Regulatory/approval | CE/FCC/UL 62368-1/E-mark |
| RoHS                | Yes                      |

## People & Technology. Connected.

We are a people company. Our experienced, skilled and passionate people empower you to meet your challenges through best-in-class, user-friendly solutions. We are a technology company. We help you optimize processes through our software, hardware and services, and through our support. Connecting people and technologies gives you the means to accomplish your goals and ambitions, and gain a competitive edge in today's digitalized world.

Visiting address HQ: Stora Varvsgatan 13a

SE - 211 75 Malmö, SWEDEN

[+46 40 35 86 00](tel:+4640358600) (tel:+46 40 35 86 00)

[info@beijerelectronics.com](mailto:info@beijerelectronics.com) (mailto:info@beijerelectronics.com)