
KEMET Part Number: SN8D-500

(UALSN8D5000000)



KEMET, SN, AC Line Filters, Normal Mode, 125 uH, MIN



Dimensions		
D	17mm MAX	
Н	13mm MAX	
LL	20mm +/-2mm	
S	10.5mm NOM	
L2	1.5mm MAX	

Packaging Specifications		
Packaging:	Bulk	
Packaging Quantity:	1800	
Weight:	7.3 g	

General Information		
Series:	SN	
Style:	Through-Hole	
Features:	Compact Size	
RoHS:	Yes	
Miscellaneous:	27 (K) Temperature Rise Max.	

Specifications		
Inductance:	125 uH (0.1 MHz)	
Inductance Tolerance:	MIN	
Current:	2 A	
Temperature Range:	-25/+105°C	
DC Resistance:	100 mOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

