

Eaton 12BFGHA16

Catalog Number: 12BFGHA16

Eaton Bussmann series Air fuse-link, medium voltage, 16 A, AC 12 kV, 359 x 76.2 mm, back-up, BS, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	12BFGHA16
	UPC
	051712241038
EAN	Product Length/Depth
5027590431750	359 mm
Product Height	Product Width
76.2 mm	76 mm
Product Weight	Warranty
4200 g	Not Applicable
Compliances	
BS 2692-1	

Product specifications

Used with

A3354730 Fuse clip

Type

Fuse

Application

protection of primary side
transformers
used in fuse switch
combination units, fuse
bases and fuse switches

Amperage Rating

16 A

Fuse indicator

With Striker

Fuse size

76 x 359 mm

Breaking capacity

40 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

Resources

Catalogs

12BFGHA16~Eaton Bussmann series medium voltage BS air fuse

Bussmann series complete full line catalog no. 1007

With striker

Yes

Class

Class back-up

Barrels

1

Construction type

Bolt-on

Fuse shape

Cylindrical

Element

Silver

Fuse diameter

76 mm

Interrupt rating

40 kAIC

Construction size

76 x 359 mm

Mounting method

Clip-in

Voltage rating

12 kV

Fuse type

BFGH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia