

WIB 4

Surface Sealed Box - Black



Products may differ in size, colour and appearance to those shown. If you require further information or customisation, please contact us directly.

Material	Thermoplastic
Protection class	IP65
Temp. range min	-25 °C
Temp. range max	85 °C
Temperatures during install.	-5°C - 60°C
Glow wire test	650 °C
Impact resistance	IK08
External dimensions LxWxH	230x180x88mm
Type	WIB 4
UK-Number	886N
Product Color	RAL 9005
WISKA-Order no.	10104635
Packing unit	1

Description:

1/4 turn fast screw system
1 screw attached to lid
Tamper-proof seal
smooth sides

Recommended accessories

PM886/1	10104692
----------------	----------

17.08.2026

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

☎ +44-12-08816062 · 📠 +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk