



Item # LC1D656BD, Old Type TeSys D IEC Contactor - 65A - Vdc Coil

TeSys D IEC Contactor - 65A - 24Vdc Coil

Specifications

Termination Method	Ring Tongue
Contact Rating	600V / 65A
Coil Voltage	24Vdc
Std. DC Voltage Code	BD
Low Consumption DC Voltage Code	N/A
Coil Consumption Inrush	22 W
Coil Consumption Sealed	22 W
Power Wire Size	Lug Size 0.32 in (8 mm)
Power Terminal Torque	54 lb-in (6 Nm)
Control Wire Size	#10 - #18 AWG
Control Terminal Torque	15 lb-in (1.7 Nm)
Mounting Hardware	35mm DIN Rail, #8 screw
Weight	4.74 lb (2.11 kg)
AC1 Resitive Rating	80 Amp
AC3 Inductive Rating	65 Amp
AC3 Single Phase 115V	5 HP
AC3 Single Phase 230V	10 HP
AC3 Three Phase 200V	20 HP
AC3 Three Phase 230V	20 HP
AC3 Three Phase 460V	40 HP
AC3 Three Phase 575V	50 HP
Control Contact Rating (1NC/0NO)	A600
UL File/CCN	E164862 / NLDX
CSA File	LR43364 3211 04
Meets Standard	IEC 60647-4
CE	Yes
RoHS	Yes