

56612

Dustpan set, closable with broom, 370 mm, Green



Sweep up and collect dry and moist debris in the same smooth, even movement. Angle-cut broom head features two kinds of bristles, and the closeable dustpan has a solid contact lip to gather up debris easily and effectively.

Technical Data

Item Number	56612
Material	Polypropylene Polyester Stainless Steel (AISI 304) Anodised Aluminium
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	4 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	54 Pcs.
Quantity Per Layer (Pallet)	8 Pcs.
Box Length	840 mm
Box Width	410 mm
Box Height	370 mm
Length/Depth	370 mm
Width	240 mm
Height	1170 mm
Gross Weight	1,918 kg
Net Weight	1,693 kg
Cubik metre	0,0402 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Symbol "5", Polypropylene (PP)	Yes
GTIN-13 Number	5705022015296
GTIN-14 Number (Box quantity)	15705028015358
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its

intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.