

FEATURES

- **Sintered Bronze Material:** Provides high wear resistance and longevity
- **Flanged Design:** Ensures secure positioning and easy installation
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying loads
- **Static Load Rating of 50 N/mm²:** Capable of handling significant static loads
- **Bore Size of 50.04 mm:** Compatible with a wide range of shafts
- **Outside Diameter of 60.09 mm:** Fits standard housing dimensions
- **Width of 40 mm:** Offers stability and support

RS PRO 50.04 mm Flanged Plain Bearing

RS Stock No: 528-805



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. Its primary benefit is the ability to support both dynamic and static loads effectively.

General Specifications

Bore Size	50.04 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	60.09 mm
Width	40 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

