



PRODUCT-DETAILS

CA5-31N

CA5-31N Auxiliary Contact Block



概要信息	
产品型号	CA5-31N
产品ID	1SBN010040R1231
欧洲商品编号(EAN)	3471522199263
目录说明	CA5-31N Auxiliary Contact Block
详细描述	CA5-31N is a 4-pole front mounted auxiliary contact block equipped with screw terminals. CA5-...M version offers terminal assortment matching the marking of 4-pole N contactor relays. CA5-31N is available with 3 N.O. and 1 N.C. instantaneous contacts for standard industrial environments.

订货信息	
最小起订量	2 piece
海关关税号	85389099

Popular Downloads	
数据手册, 技术资料	1SBC100214C0202
说明书和手册	1SBC101012M5501

尺寸

产品净宽	43 mm
产品净深	39 mm
产品净高	47 mm
产品净重	0.06 kg

技术参数

辅助触点NO数量	3
辅助触点NC数量	1
额定工作电压	Auxiliary Circuit 690 V
额定频率 (f)	Auxiliary Circuit 50 / 60 Hz
额定工作电流 AC-15 (I _e)	(500 V) 2 A (690 V) 2 A (24 / 127 V) 6 A (220 / 240 V) 4 A (380 / 400 V) 3 A
短路保护设备	Auxiliary Circuit - gG Type Fuses 10 A
额定不间断电流 (I _{cw})	for 0.1 s 140 A for 1 s 100 A
最高电气切换频率	1200 cycles per hour
额定工作电流 DC-13 (I _e)	(24 V) 6 A / 144 W (48 V) 2.8 A / 134 W (72 V) 1 A / 72 W (110 V) 0.55 A / 60 W (125 V) 0.55 A / 69 W (220 V) 0.30 A / 66 W (250 V) 0.3 / 75 W
额定绝缘电压 (U _i)	acc. to IEC 60947-5-1 690 V acc. to UL/CSA 600 V
机械寿命	10 million
最高机械切换频率	3600 cycles per hour
防护等级	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
端子类型	Screw Terminals
适用于	N22E N31E N40E NL22E NL31E NL40E TNL22E TNL31E TNL40E

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS信息	2CMT2021-006277
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
WEEE B2C / B2B	Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

认证及声明（文件编码）	
CB认证	CB_SE_62119A1
CCC认证	CCC_2015010304800518
CQC认证	CQC2015010304800518 CQC2004010305133985
CSA 认证	CSA_1033838
Declaration of Conformity - CCC	2020980304001627 2020980305001185
符合性声明 - CE	1SBD250809U1000
Declaration of Conformity - UKCA	1SBD250826U1000
DNV GL Certificate	DNV_GL_TAE00001UT
EAC认证	EAC_RU C-FR ME77 B03391
GOST认证	GOST_POCCFRME77B07174
RINA认证	RINA_ELE172319XG001
UL认证	UL_071301E48139

包装信息	
1级包装单元	box 2 piece
1级包装宽度	65 mm
1级包装长度	129.5 mm
1级包装高度	43 mm
1级包装 总重	0.12 kg
1级包装 EAN	3471522199263
2级包装单元	box 200 piece
2级包装宽度	300 mm
2级包装长度	245 mm
2级包装高度	308 mm
2级包装 总重	12 kg
3级包装单元	3600 piece

分类	
对象分类代码	K
ETIM 7	EC000041 - Auxiliary contact block
ETIM 8	EC000041 - Auxiliary contact block
ETIM 9	EC000041 - Auxiliary contact block
e级	V11.0 : 27371302
UNSPSC	39121522
IDEA 粒度分类代码 (IGCC)	4743 >> Auxiliary contact block

分类

低压产品及系统 → 控制产品 → 接触器 → 模块化接触器

