

Features

- Nickel-plated brass adaptors
- All Fluids compatible
- High performances in pressure and temperatures
- Mechanical Resistance
- Silicon Free

Hose Connector Hose Tail Adaptor

RS Stock No.:

0665596, 0665597



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Product type: Brass male hose adaptor (taper thread)
- Applications: Compressed Air - Pneumatic Automation - Industrial water circuits - Inert Gases, Fluids, Steam - Vacuum
- Materials: the main part of these fittings is made in OT UNI EN 12164/5 CW 614/7N and undergo to a nickel-plating process.
- Compatibility: Water / Oils / Compressed air Fluids in general for the hydraulic, pneumatic and oil dynamic plants etc.
- Threads: tapered gas in conformity with ISO7.1, BS 21, DIN 2999

General Specifications

Hose Inner Diameter	See below detailed table
Thread Size	See below detailed table
Thread Standard	BSPT
Hose Connector Type	Hose Tail Adaptor
Body Material	Nickel Plated brass CW614/7N
Connector Gender	Male
Valved	No
Coupling Connector Direction	Straight
Thread Standard	ISO7.1, BS 21, DIN 2999
Maximum Working Pressure	100 bar

Approvals

Declarations	MFR Declaration of Conformity
Standards Met	REACH 1907/2006 - PED 2014/68/UE - RoHS 2011/65/CE

Specifications

Code	A Hose Inner Diameter (mm)	A1 Thread Size	B (mm)	C (mm)	L (mm)	CH (mm)	Bag (mm)
0665596	6	1/4"	19.5	11	35.5	14	10
0665597	12	1/2"	19.5	14	39	22	10

