

Features

- Commercial strength box section construction with twist proof rung joints
- Reduce fatigue with deep, comfortable D-shaped rungs
- Slip-resistant high traction rungs
- Stabilising bar supplied with ladder - requires fitting before first use
- Anti-slip rubber feet
- *Please note that the 2.5m & 3.0m Single Section Ladders do not require a stabiliser bar for use

RS PRO 4.0m Professional Double Extension Ladder

RS Stock No.: 0285127



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Optimised for professional and trade use, the RS PRO ladder offers unparalleled quality for industrial and trade users. It is manufactured to the latest EN131 Professional standards and is supplied with a stabiliser bar for enhanced stability and safety. Please note the bar requires fitting before the first use, and once fitted, it must not be removed from the ladder. Crafted from lightweight yet robust aluminium, the ladder provides a secure platform for a safer working experience. It boasts thicker box section stiles than most alternatives, reducing the likelihood of twisting and ensuring longevity. Proudly manufactured in the UK, the RS PRO ladder comes with an extended 3-year warranty, promising durability and service for years to come. Please be advised, recent standard changes mean that the sections of this ladder are now permanently affixed and cannot be separated.

General Specifications

Max Load	150kg
Standard	EN131 PROFESSIONAL
Material	Aluminium
Commodity Code	76169990
Country of Origin	UK
Recommended Usage	Regular

Similar Products

Stock No.	Rungs /Sections	Last Climbing Height (mm)	Approx. Working Height [†] (mm)	Closed Length (mm)	Extended Length (mm)	Width (mm) S	Stabiliser Bar Width (mm)	Depth (mm)	Nett Weight (kg)
0285167	9 x 2	2800	4550	2500	3970	410	1200	142	12.3
0285124	11 x 2	3700	5450	3000	5000	410	1200	142	14.4
0285126	13 x 2	4700	6450	3500	6000	410	1200	160	16.4
0285127	15 x 2	5700	7450	4000	7000	410	1200	160	24.8†
0285128	9 x 3	4300	6050	2500	5500	485	1200	220	18.0
0285130	11 x 3	5700	7450	3000	7000	485	1200	245	28.3†
0285132	13 x 3	7200	8950	3500	8500	485	1200	245	32.7†
0285133	15 x 3	8600	10350	4000	9900	485	1200	245	37.1

[†] Heavy Item – 2-person lift required.

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

